

# CRYSTALITE MATT BRUSH-ON GLAZES

Introducing the new Chrysanthos Crystalite Brush-on Glazes. A range of unleaded intermixable brush-on glazes. A range of decorative matt finishes highlighted by a splattering of tiny glass flecks. All offer superlative value.



CR001  
WHITE  
140ml



CR005  
BRIGHT YELLOW  
140ml



CR013  
PERSIMMON  
140ml



CR017  
CORAL RED  
140ml



CR025  
BURGUNDY  
140ml



CR029  
JASPER  
140ml



CR033  
JADE GREEN  
140ml



CR037  
APPLE  
140ml



CR041  
BRUNSWICK GREEN  
140ml



CR049  
SUMMER BLUE  
140ml



CR053  
COBALT BLUE  
140ml



CR057  
IRIS PURPLE  
140ml



CR061  
GREY  
140ml



CR065  
TERRACOTTA  
140ml



CR069  
COBALT BLACK  
140ml

Crystallite Glazes are unleaded and come in a range of decorative matt finishes highlighted by a splattering of tiny glass flecks, giving a slightly textured surface finish. They have a firing range of 1000-1060°C (cone 06-04). Available in 140ml jars. All glazes in the range are unleaded and fully intermixable.



Morells Barn • Park Lane • Lower Bognor Road • Lagness • Chichester • West Sussex • PO20 1LR  
Telephone: 01243 265845 • Fax: 01243 267582 • email: [info@claymansupplies.co.uk](mailto:info@claymansupplies.co.uk) • [www.claymansupplies.co.uk](http://www.claymansupplies.co.uk)

# CLAYMAN

where quality comes as standard

# CRYSTALLITE GLAZES

- Matt colours with fragments of embedded clear crystals
- Firing range is cone 06 (1000°C) to cone 04 (1060°C)
- 3 coat application to greenware or bisque
- All colours are fully intermixable
- Available in 140ml sizes

## USAGE

Crystallite Glazes are unleaded and come in a range of decorative matt finishes highlighted by a spattering of tiny glass flecks, giving a slightly textured surface finish.

## APPLICATION

Before use, mix glaze well, stirring or shaking to distribute crystals evenly.

To obtain optimum results, 3 coats of Crystallite Glazes should be applied using a well-loaded glaze brush. Ensure each coat is dry before applying subsequent coats at right angles to one another (i.e. crosshatching). Alternately 3 coats may be applied with a sponge.

Crystallite Glazes are typically not glazed over.

## PHYSICAL DATA

The Crystallite Glazes should be fired between cone 06 to 04 (1000°C to 1060°C). If the Crystallite Glazes are fired higher, the colour heightens and the crystals further expand.

## SAFETY DATA

These products are unsuitable for use on food or beverage containers since the finished product remains unglazed and consequently porous.

Also available in the Chrysanthos range of products is Superior Glazes, Hobby Brush-on and Dipping Glaze, 3D Trailing Colours and Cafe Underglaze Colours