

# 3D TRAILING GLAZES

Introducing the new Chrysanthos 3D Trailing Glazes. A range of unleaded, thick textured trailable glaze designed for creating raised linear decoration.



3D005 - YELLOW  
40ml • 500ml



3D009 - ORANGE  
40ml • 500ml



3D013 - RED  
40ml • 500ml



3D017 - GREEN  
40ml • 500ml



3D021 - BLUE  
40ml • 500ml



3D025 - BLACK  
40ml • 500ml

3D Trailing Glazes can be used on both greenware and bisque, in conjunction with underglaze decoration, or on top of unfired glaze. They can be left unglazed, or may be covered with coloured or clear glaze. They can achieve stability and versatility, without cracking and are available in a convenient nozzle squeeze bottle.



Morells Barn • Park Lane • Lower Bognor Road • Lagness • Chichester • West Sussex • PO20 1LR  
Telephone: 01243 265845 • Fax: 01243 267582 • email: [info@claymansupplies.co.uk](mailto:info@claymansupplies.co.uk) • [www.claymansupplies.co.uk](http://www.claymansupplies.co.uk)

# CLAYMAN

where quality comes as standard

## 3D TRAILING GLAZES

- Unleaded slip trailing glazes
- Firing range is cone 06 (1000°C) to cone 03 (1101°C)
- Suitable for greenware and bisque
- All colours are fully intermixable
- Available in 40 ml, 500 ml sizes

### USAGE

3D Trailing Glazes are unleaded and are a thick textured trailable glaze designed for creating raised linear decoration. They can be used on both greenware and bisque, in conjunction with underglaze decoration, or on top of unfired glaze. They can be left unglazed, or may be covered with coloured or clear glaze.

3D Trailing Glazes achieve stability and versatility, without cracking and are available in a convenient nozzle squeeze bottle

To create more colours than those available, colours may be intermixed. This is achieved by squeezing colours to be mixed into a pallet and mixing with a clean brush or pallet knife. The colour may then be scooped back into a bottle that has been cleaned.

### APPLICATION

Shake the applicator bottle well and always test on paper to ensure 3D Trailing Glaze flows correctly before attempting to decorate ware.

If glaze appears too thick, add a few drops of clean water and shake to combine thoroughly.

If applicator nozzle is blocked, remove and wash in hot water using paper clip wire to dislodge blockage. Dry nozzle before re-attaching it to the bottle.

To apply, gently squeeze the bottle with the applicator tip above (and not touching) the ceramic surface. If applying to bisque, allow slip trail decoration to dry thoroughly before glazing over.

### PHYSICAL DATA

3D Trailing Glazes may be fired between cone 06 to 03 (1000°C to 1101°C) without significant flattening of the raised decoration.

Also available in the Chrysanthos range of products is Superior Glazes, Hobby Brush-on and Dipping Glaze, 3D Trailing Colours and Cafe Underglaze Colours